## **Divalent Metal Doped Absorbing layers for Perovskite Solar Cells**

P. Palanichamy <sup>1</sup>, S. Pitchaiya <sup>1</sup>, A. Santhanam <sup>1</sup>, M. Natarajan <sup>1</sup> V. Dhayalan Velauthapillai <sup>2</sup>

<sup>1</sup>Department of Physics, Coimbatore Institute of Technology, Coimbatore, TamilNadu, India. <sup>2</sup>Faculty of Engineering, Western Norway University of Applied Sciences, Bergen, Norway. Email: pavipalanichamy@gmail.com, santhanam.agilan@gmail.com

## Abstract

Perovskite solar cells (PSC) having a unique crystal structure of ABX<sub>3</sub> (A-Monovalent Cation, B-Divalent Cation, X-Halogen anion) that provides good power conversion efficiency (PCE) in cost-effective photovoltaic. The main reason for its crucial role in today's photovoltaic is its rapidly increased PCE up to 22.1% within a few years. This highest PCE obtained by only using lead (Pb) as light absorbing material; although, chemical instability and environmental hazards of lead are still a big challenge. Stability can be improved by modifying the halogen ions (Cl-, Br- and I-) and exchanging divalent cation (CH<sub>3</sub>NH<sub>3</sub>I). Even the percentage of lead consumption in perovskite is low, but it causes more harm to the environment and also acts as a carcinogenic agent for humans due to its water solubility and chemical instability. In the path of lead-free perovskite solar cells, we made a try of doping divalent metals with the Pb as an absorbing layer and analysed. The absorbance of the active layer is analysed by UV-Visible spectrophotometer. X-Ray Diffractometer result confirms the structure of perovskite. I-V characteristics of fabricated PSC device have been analysed by Keithley Source Meter-2450.